
፼ GIMA


FURN<u>ITURE</u>



ILLUMINATED AND NOT ILLUMINATED OPTOMETRIC CHARTS

	MOLA OTIMETICA DOMALE MARCINE		Hand an anter ante	The second secon	according to extra white reading of a screen, and Shuko plug,
TRLPEMU FOBE UES LXMFF AEA FOFE UES LXMFF AEA FOFE AEA FOFE AEA FOFE AEA FOFE AEA	*** B G L Y C K I *** * H D F Z X X *** * H D F Z X X *** * D L Y H C H *** * D L Y H C H *** * D L Y H C H *** *** * D L Y H C H *** *** * D L Y H C H *** *** *** * T T T T *** <t< th=""><th>•••• () •••• () ••• () ••• () •• () •• (</th><th>и калала (и хахала (и хахала (и Жачча (и Жачча (</th><th>OLUHC PRBTNA DFLÄHTE NCTFÜBLR FFUBLR CFRUÄTISC DOTRÜBLR</th><th>Viewing Are External dim Weight: 6 kg Other specif</th></t<>	•••• () •••• () ••• () ••• () •• () •• (и калала (и хахала (и хахала (и Жачча (и Жачча (OLUHC PRBTNA DFLÄHTE NCTFÜBLR FFUBLR CFRUÄTISC DOTRÜBLR	Viewing Are External dim Weight: 6 kg Other specif
	··········		5005 XXX-4X-4X W	antreitarea .	OPTOMETR
MIXED DECIMAL 3m • 27382	MONOYER 3m • 27381	CHILDREN 3m • 27383	ANIMALS 5.5m • 27384	ARMAGNAC 5m • 27380	Armagnac Monoyer - Mixed deci Children - Animals - 5

GIMA luminous optotypes have been designed according to clinical recommendations for an extra white light to give an accurate and precise reading of any detail.Manufactured with acrylic screen, and according to safety norms (fuses, Shuko plug, green light On/Off,...)



27388

Spare Tube 700

_